



Ultra-low-power, smart-metering MCUs with precision analog, security and HMI peripherals

## KM Series MCUs

KM series MCUs are based on the 32-bit Arm® Cortex®-M0+ core and provide a low-cost, highly integrated solution for one-, two- and three-phase electricity meters that require powerful 32-bit processing capability, precision analog, security, and HMI functionality.

### TARGET APPLICATIONS

- ▶ Electricity meters
- ▶ Flow meters (e.g., heat, water, gas)
- ▶ Industrial measurement and sensing

Each MCU includes a powerful analog front end that is configurable for different regions, enabling power calculations with 0.1 percent accuracy. A high-accuracy, real-time clock delivers less than 5 PPM drift over temperature. Metrology firmware for calculating active, reactive and apparent power using a variety of algorithms is provided free of charge. Pre-certified reference designs for Europe, China, India, the U.S. and Japan are available for customer evaluation.

The KM series is supported by the Tower System hardware development platform.

### SPECIFICATIONS

#### KM series MCUs

- ▶ High-performance Cortex-M0+ core, up to 75 MHz of core clock frequency
- ▶ 512/256/128/64 KB single array flash
- ▶ Supports v6-M instruction set architecture including all 16-bit v7-M instructions plus a number of 32-bit Thumb®-2 instructions

- ▶ Phase-locked loop to generate clocks for analog front end
  - Input range: 31.25–39.0625 kHz
  - Output range: 11.72–14.65 MHz
- ▶ Frequency-locked loop to generate core, system and flash clocks
  - Input range: 31.25–39.0625 kHz
  - Output range: 20–50 MHz
- ▶ Flexible modes of operation
- ▶ Two internal trimmable clock references
  - 32 kHz
  - 4 MHz



## Analog front end

- ▶ 24-bit sigma-delta ADC with 94 dB SNR
- ▶ Programmable gain amplifier with gains from 1 to 32 with low temperature drift
- ▶ High precision internal voltage reference with low temperature drift
- ▶ Up to 16-channel, 16-bit SAR ADC

## Security

- ▶ Memory mapped cryptographic acceleration unit (MMCAU) for AES encryption
- ▶ Memory protection unit, AIPS (peripheral protection), random number generator, CRC

## Interface

- ▶ LCD segment driver up to 448 (56 x 8) segments
- ▶ High accuracy RTC +5 PPM over temperature range
- ▶ Up to five UART, three SPI, two I<sup>2</sup>C


## Other specifications

- ▶ Voltage range: 1.71–3.6 V (without AFE)
- ▶ Voltage range: 2.7–3.6 V (with AFE)
- ▶ Temperature range: –40 °C to +105 °C

## KEY FEATURES

- ▶ High-performance ultra-low-power Cortex-M0+ core
- ▶ 24-bit sigma-delta ADC and PGA achieving 94 dB SNR
- ▶ High accuracy RTC with +5 PPM over temperature
- ▶ Rich set of security: MPU, active tamper, RNG for Welmecc compliant meters
- ▶ Pre-certified metrology software

## KM MCU SERIES BLOCK DIAGRAM



## ENABLEMENT

- ▶ TWR-KM35Z75M/TWR-KM34Z75M/TWR-KM34Z50M Tower® System development module
- ▶ Reference designs (available for loan)
  - Low-cost three-phase/single-phase power meters for markets in Asia
  - Three-phase/single-phase power meters for markets in EMEA
  - Two-phase power meter for markets in AMR/JPN
- ▶ MCUXpresso SDK - an extensive suite of robust peripheral drivers, stacks and middleware
- ▶ IAR Embedded Workbench®, Arm Keil® MDK IDEs and others from the Arm technology ecosystem
- ▶ Proprietary MQX™ Lite RTOS
- ▶ Application notes
- ▶ Tower System development platform

## KM SERIES SELECTOR GUIDE

Sub-Family	Part Number	CPU Frequency (MHz)	Flash (KB)	SRAM (KB)	UART (ISO 7816/LPUART)	I <sup>2</sup> C	SPI	ADC (24-bit (ΣΔ))	Total I/Os	Package				Development Hardware
										HH	LH	LL	LQ	
										44 LGA (5 x 5, 0.65 mm)	64 LQFP (10 x 10, 0.5 mm)	100 LQFP (14 x 14, 0.5 mm)	144 LQFP (20 x 20, 0.5 mm)	
KM14	MKM14Z128(A)xxx5	50	128	16	2 (2 / -)	1	2	4	20	Y				TWR-KM34Z50M(V3)
	MKM14Z64(A)xxx5	50	64	16	2 (2 / -)	1	2	4	20	Y				TWR-KM34Z50M(V3)
KM33	MKM33Z128(A)xxx5	50	128	16	4 (2 / -)	2	2	3	38-68		Y	Y		TWR-KM34Z50M(V3)
	MKM33Z64(A)xxx5	50	64	16	4 (2 / -)	2	2	3	38-68		Y	Y		TWR-KM34Z50M(V3)
KM34	MKM34Z128(A)xxx5	50	128	16	4 (2 / -)	2	2	4	68			Y		TWR-KM34Z50M(V3)
	MKM34Z256xxx7	75	256	32	5 (2 / 1)	2	2	4	72-99			Y	Y	TWR-KM34Z75M
KM35	MKM35Z256xxx7	75	256	64	5(2/1)	2	3	4	72-99			Y	Y	TWR-KM35Z75M
	MKM35Z512xxx7	75	512	64	5(2/1)	2	3	4	72-99			Y	Y	TWR-KM35Z75M

[www.nxp.com/KMseries](http://www.nxp.com/KMseries)

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. Arm and Cortex are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2020 NXP B.V.

Document Number: KNTSKM3XFS REV 6